

Develosil 30 (Silica)

Part number	Brand name	Stationary phase	um	Column category	i.d.	mm	price (yen)	
S030320050W	Develosil	30-3 (Silica)	3	Semi micoro	2.0	50	30,000	
S030320100W	Develosil	30-3 (Silica)	3	Semi micoro	2.0	100	35,000	
S030320150W	Develosil	30-3 (Silica)	3	Semi micoro	2.0	150	40,000	
S030320250W	Develosil	30-3 (Silica)	3	Semi micoro	2.0	250	50,000	
S030520050W	Develosil	30-5 (Silica)	5	Semi micoro	2.0	50	25,000	
S030520100W	Develosil	30-5 (Silica)	5	Semi micoro	2.0	100	35,000	
S030520150W	Develosil	30-5 (Silica)	5	Semi micoro	2.0	150	38,000	
S030520250W	Develosil	30-5 (Silica)	5	Semi micoro	2.0	250	48,000	
S030346050W	Develosil	30-3 (Silica)	3	Analysis column	(Conventional Column)	4.6	50	30,000
S030346100W	Develosil	30-3 (Silica)	3	Analysis column	(Conventional Column)	4.6	100	35,000
S030346150W	Develosil	30-3 (Silica)	3	Analysis column	(Conventional Column)	4.6	150	40,000
S030346250W	Develosil	30-3 (Silica)	3	Analysis column	(Conventional Column)	4.6	250	50,000
S030546050W	Develosil	30-5 (Silica)	5	Analysis column	(Conventional Column)	4.6	50	25,000
S030546100W	Develosil	30-5 (Silica)	5	Analysis column	(Conventional Column)	4.6	100	35,000
S030546150W	Develosil	30-5 (Silica)	5	Analysis column	(Conventional Column)	4.6	150	38,000
S030546250W	Develosil	30-5 (Silica)	5	Analysis column	(Conventional Column)	4.6	250	48,000
S030746150W	Develosil	30-7 (Silica)	7	Analysis column	(Conventional Column)	4.6	150	33,000
S030746250W	Develosil	30-7 (Silica)	7	Analysis column	(Conventional Column)	4.6	250	43,000
S031046150W	Develosil	30-10 (Silica)	10	Analysis column	(Conventional Column)	4.6	150	35,000
S031046250W	Develosil	30-10 (Silica)	10	Analysis column	(Conventional Column)	4.6	250	40,000
S030580250W	Develosil	30-5 (Silica)	5	Semi-preparative		8.0	250	85,000
S0305P1250W	Develosil	30-5 (Silica)	5	Semi-preparative		10.0	250	115,000
S030780250W	Develosil	30-7 (Silica)	7	Semi-preparative		8.0	250	80,000
S0307P1250W	Develosil	30-7 (Silica)	7	Semi-preparative		10.0	250	110,000
S031080250W	Develosil	30-10 (Silica)	10	Semi-preparative		8.0	250	75,000
S0310P1250W	Develosil	30-10 (Silica)	10	Semi-preparative		10.0	250	105,000
S0305P2250W	Develosil	30-5 (Silica)	5	preparative		20.0	250	180,000
S0307P2250W	Develosil	30-7 (Silica)	7	preparative		20.0	250	165,000
S0310P2250W	Develosil	30-10 (Silica)	10	preparative		20.0	250	150,000

Develosil 30 (Silica) Guard column

Part number	Brand name	Stationary phase	um	Column category	I.D.	mm	price (yen)		
							old price	New price	
cartridge type									
HO00015010C	Develosil	Guard cartridge holder		Holder for the guard cartridge	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	15,000	18,000
HO00040010C	Develosil	Guard cartridge holder		Holder for the guard cartridge	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	9,500	13,000
S030515010W	Develosil	30-S (Silica) Guard cartridge set Holder(1piece) + cartridge 10 x 1.5mm (1piece)	5	The gured column	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10		25,500
	Develosil	30-S (Silica) Guard cartridge 【8/pk】		The cartridge for exchange	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	40,000	
S030515010C	Develosil	30-S (Silica) Guard cartridge 【4/pk】	5	The cartridge for exchange	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10		30,000
S030540010W	Develosil	30 (Silica) Guard cartridge set Holder(1piece) + cartridge 10 x 4.0mm	5	The gurad column	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10		24,000
	Develosil	30 (Silica) Guard cartridge 【8/pk】		The cartridge for exchange	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	36,000	
S030540010C	Develosil	30 (Silica) Guard cartridge 【4/pk】	5	The cartridge for exchange	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10		30,000
filling type									
S030546010W	Develosil	30-5 (Silica)	5	The gurad column	for i.d. 4.0mm,4.6mm and 6.0mm	4.6	10	14,000	no change
S030780010W	Develosil	30-7 (Silica)	7	The gurad column	for i.d. 4.0mm,4.6mm and 6.0mm	4.6	10	14,000	no change
S031046010W	Develosil	30-10 (Silica)	10	The gurad column	for i.d. 4.0mm,4.6mm and 6.0mm	4.6	10	14,000	no change
S030580010W	Develosil	30-5 (Silica)	5	The gurad column	for i.d. 8.0mm and 10.0mm	8.0	10	20,000	no change
S030780010W	Develosil	30-7 (Silica)	7	The gurad column	for i.d. 8.0mm and 10.0mm	8.0	10	20,000	no change
S031080010W	Develosil	30-10 (Silica)	10	The gurad column	for i.d. 8.0mm and 10.0mm	8.0	10	20,000	no change
S0305P2050W	Develosil	30-5 (Silica)	5	The gurad column	for i.d. 20.0mm	20.0	50	80,000	no change
S0307P2050W	Develosil	30-7 (Silica)	7	The gurad column	for i.d. 20.0mm	20.0	50	80,000	no change
S0310P2050W	Develosil	30-10 (Silica)	10	The gurad column	for i.d. 20.0mm	20.0	50	80,000	no change

Develosil 60 (Silica)

Part number	Brand name	Stationary phase	um	Column category	i.d.	mm	price (yen)	
S060320050W	Develosil	60-3 (Silica)	3	Semi micoro	2.0	50	30,000	
S060320100W	Develosil	60-3 (Silica)	3	Semi micoro	2.0	100	35,000	
S060320150W	Develosil	60-3 (Silica)	3	Semi micoro	2.0	150	40,000	
S060320250W	Develosil	60-3 (Silica)	3	Semi micoro	2.0	250	50,000	
S060520050W	Develosil	60-5 (Silica)	5	Semi micoro	2.0	50	25,000	
S060520100W	Develosil	60-5 (Silica)	5	Semi micoro	2.0	100	35,000	
S060520150W	Develosil	60-5 (Silica)	5	Semi micoro	2.0	150	38,000	
S060520250W	Develosil	60-5 (Silica)	5	Semi micoro	2.0	250	48,000	
S060346050W	Develosil	60-3 (Silica)	3	Analysis column	(Conventional Column)	4.6	50	30,000
S060346100W	Develosil	60-3 (Silica)	3	Analysis column	(Conventional Column)	4.6	100	35,000
S060346150W	Develosil	60-3 (Silica)	3	Analysis column	(Conventional Column)	4.6	150	40,000
S060346250W	Develosil	60-3 (Silica)	3	Analysis column	(Conventional Column)	4.6	250	50,000
S060546050W	Develosil	60-5 (Silica)	5	Analysis column	(Conventional Column)	4.6	50	25,000
S060546100W	Develosil	60-5 (Silica)	5	Analysis column	(Conventional Column)	4.6	100	35,000
S060546150W	Develosil	60-5 (Silica)	5	Analysis column	(Conventional Column)	4.6	150	38,000
S060546250W	Develosil	60-5 (Silica)	5	Analysis column	(Conventional Column)	4.6	250	48,000
S060746150W	Develosil	60-7 (Silica)	7	Analysis column	(Conventional Column)	4.6	150	33,000
S060746250W	Develosil	60-7 (Silica)	7	Analysis column	(Conventional Column)	4.6	250	43,000
S061046150W	Develosil	60-10 (Silica)	10	Analysis column	(Conventional Column)	4.6	150	35,000
S061046250W	Develosil	60-10 (Silica)	10	Analysis column	(Conventional Column)	4.6	250	40,000
S060580250W	Develosil	60-5 (Silica)	5	Semi-preparative		8.0	250	85,000
S0605P1250W	Develosil	60-5 (Silica)	5	Semi-preparative		10.0	250	115,000
S060780250W	Develosil	60-7 (Silica)	7	Semi-preparative		8.0	250	80,000
S0607P1250W	Develosil	60-7 (Silica)	7	Semi-preparative		10.0	250	110,000
S061080250W	Develosil	60-10 (Silica)	10	Semi-preparative		8.0	250	75,000
S0610P1250W	Develosil	60-10 (Silica)	10	Semi-preparative		10.0	250	105,000
S0605P2250W	Develosil	60-5 (Silica)	5	preparative		20.0	250	180,000
S0607P2250W	Develosil	60-7 (Silica)	7	preparative		20.0	250	165,000
S0610P2250W	Develosil	60-10 (Silica)	10	preparative		20.0	250	150,000

Develosil 60 (Silica) Guard column

Part number	Brand name	Stationary phase	um	Column category	I.D.	mm	price (yen)		
							old price	New price	
cartridge type									
HO00015010C	Develosil	Guard cartridge holder		Holder for the guard cartridge	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	15,000	18,000
HO00040010C	Develosil	Guard cartridge holder		Holder for the guard cartridge	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	9,500	13,000
S060515010W	Develosil	60-S (Silica) Guard cartridge set Holder(1piece) + cartridge 10 x 1.5mm (1piece)	5	The gured column	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	20,000	25,500
S060515010C	Develosil	60-S (Silica) Guard cartridge 【4/pk】	5	The cartridge for exchange	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	20,000	30,000
S060540010W	Develosil	60 (Silica) Guard cartridge set Holder(1piece) + cartridge 10 x 4.0mm	5	The gurad column	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	14,000	24,000
S060540010C	Develosil	60 (Silica) Guard cartridge 【4/pk】	5	The cartridge for exchange	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	18,000	30,000
filling type									
S060580010W	Develosil	60-5 (Silica)	5	The gurad column	for i.d. 4.0mm,4.6mm and 6.0mm	4.6	10	14,000	no change
S060780010W	Develosil	60-7 (Silica)	7	The gurad column	for i.d. 4.0mm,4.6mm and 6.0mm	4.6	10	14,000	no change
S061046010W	Develosil	60-10 (Silica)	10	The gurad column	for i.d. 4.0mm,4.6mm and 6.0mm	4.6	10	14,000	no change
S0605P2050W	Develosil	60-5 (Silica)	5	The gurad column	for i.d. 8.0mm and 10.0mm	8.0	10	20,000	no change
S060720050W	Develosil	60-7 (Silica)	7	The gurad column	for i.d. 8.0mm and 10.0mm	8.0	10	20,000	no change
S061080010W	Develosil	60-10 (Silica)	10	The gurad column	for i.d. 8.0mm and 10.0mm	8.0	10	20,000	no change
S0605P2050W	Develosil	60-5 (Silica)	5	The gurad column	for i.d. 20.0mm	20.0	50	80,000	no change
S0607P2050W	Develosil	60-7 (Silica)	7	The gurad column	for i.d. 20.0mm	20.0	50	80,000	no change
S0610P2050W	Develosil	60-10 (Silica)	10	The gurad column	for i.d. 20.0mm	20.0	50	80,000	no change

Develosil 100 (Silica)

Part number	Brand name	Stationary phase	um	Column category	i.d.	mm	price (yen)	
S100320050W	Develosil	100-3 (Silica)	3	Semi micoro		2.0	50	30,000
S100320100W	Develosil	100-3 (Silica)	3	Semi micoro		2.0	100	35,000
S100320150W	Develosil	100-3 (Silica)	3	Semi micoro		2.0	150	40,000
S100320250W	Develosil	100-3 (Silica)	3	Semi micoro		2.0	250	50,000
S100520050W	Develosil	100-5 (Silica)	5	Semi micoro		2.0	50	25,000
S100520100W	Develosil	100-5 (Silica)	5	Semi micoro		2.0	100	35,000
S100520150W	Develosil	100-5 (Silica)	5	Semi micoro		2.0	150	38,000
S100520250W	Develosil	100-5 (Silica)	5	Semi micoro		2.0	250	48,000
S100346050W	Develosil	100-3 (Silica)	3	Analysis column	(Conventional Column)	4.6	50	30,000
S100346100W	Develosil	100-3 (Silica)	3	Analysis column	(Conventional Column)	4.6	100	35,000
S100346150W	Develosil	100-3 (Silica)	3	Analysis column	(Conventional Column)	4.6	150	40,000
S100346250W	Develosil	100-3 (Silica)	3	Analysis column	(Conventional Column)	4.6	250	50,000
S100546050W	Develosil	100-5 (Silica)	5	Analysis column	(Conventional Column)	4.6	50	25,000
S100546100W	Develosil	100-5 (Silica)	5	Analysis column	(Conventional Column)	4.6	100	35,000
S100546150W	Develosil	100-5 (Silica)	5	Analysis column	(Conventional Column)	4.6	150	38,000
S100546250W	Develosil	100-5 (Silica)	5	Analysis column	(Conventional Column)	4.6	250	48,000
S100746150W	Develosil	100-7 (Silica)	7	Analysis column	(Conventional Column)	4.6	150	33,000
S100746250W	Develosil	100-7 (Silica)	7	Analysis column	(Conventional Column)	4.6	250	43,000
S101046150W	Develosil	100-10 (Silica)	10	Analysis column	(Conventional Column)	4.6	150	35,000
S101046250W	Develosil	100-10 (Silica)	10	Analysis column	(Conventional Column)	4.6	250	40,000
S100580250W	Develosil	100-5 (Silica)	5	Semi-preparative		8.0	250	85,000
S1005P1250W	Develosil	100-5 (Silica)	5	Semi-preparative		10.0	250	115,000
S100780250W	Develosil	100-7 (Silica)	7	Semi-preparative		8.0	250	80,000
S1007P1250W	Develosil	100-7 (Silica)	7	Semi-preparative		10.0	250	110,000
S101080250W	Develosil	100-10 (Silica)	10	Semi-preparative		8.0	250	75,000
S1010P1250W	Develosil	100-10 (Silica)	10	Semi-preparative		10.0	250	105,000
S1005P2250W	Develosil	100-5 (Silica)	5	preparative		20.0	250	180,000
S1007P2250W	Develosil	100-7 (Silica)	7	preparative		20.0	250	165,000
S1010P2250W	Develosil	100-10 (Silica)	10	preparative		20.0	250	150,000

Develosil 60 (Silica) Guard column

Part number	Brand name	Stationary phase	um	Column category	I.D.	mm	price (yen)		
							old price	New price	
cartridge type									
HO00015010C	Develosil	Guard cartridge holder		Holder for the guard cartridge	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	15,000	18,000
HO00040010C	Develosil	Guard cartridge holder		Holder for the guard cartridge	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	9,500	13,000
S100515010W	Develosil	100-S (Silica)Guard cartridge set Holder(1piece) + cartridge 10 x 1.5mm (1piece)	5	The gured column	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10		25,500
	Develosil	100-S (Silica) Guard cartridge 【8/pk】		The cartridge for exchange	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	40,000	
S100515010C	Develosil	100-S (Silica) Guard cartridge 【4/pk】	5	The cartridge for exchange	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10		30,000
S100540010W	Develosil	100 (Silica) Guard cartridge set Holder(1piece) + cartridge 10 x 4.0mm	5	The gurad column	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10		24,000
	Develosil	100 (Silica) Guard cartridge 【8/pk】		The cartridge for exchange	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	36,000	
S100540010C	Develosil	100 (Silica) Guard cartridge 【4/pk】	5	The cartridge for exchange	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10		30,000
filling type									
S100546010W	Develosil	100-5 (Silica)	5	The gurad column	for i.d. 4.0mm,4.6mm and 6.0mm	4.6	10	14,000	no change
S100746010W	Develosil	100-7 (Silica)	7	The gurad column	for i.d. 4.0mm,4.6mm and 6.0mm	4.6	10	14,000	no change
S101046010W	Develosil	100-10 (Silica)	10	The gurad column	for i.d. 4.0mm,4.6mm and 6.0mm	4.6	10	14,000	no change
S100580010W	Develosil	100-5 (Silica)	5	The gurad column	for i.d. 8.0mm and 10.0mm	8.0	10	20,000	no change
S100780010W	Develosil	100-7 (Silica)	7	The gurad column	for i.d. 8.0mm and 10.0mm	8.0	10	20,000	no change
S101080010W	Develosil	100-10 (Silica)	10	The gurad column	for i.d. 8.0mm and 10.0mm	8.0	10	20,000	no change
S1005P2050W	Develosil	100-5 (Silica)	5	The gurad column	for i.d. 20.0mm	20.0	50	80,000	no change
S1007P2050W	Develosil	100-7 (Silica)	7	The gurad column	for i.d. 20.0mm	20.0	50	80,000	no change
S1010P2050W	Develosil	100-10 (Silica)	10	The gurad column	for i.d. 20.0mm	20.0	50	80,000	no change