

## Develosil ANIDIUS

| Part number | Brand name | Stationary phase | um | Column category  | i.d.                  | mm   | price (yen) |         |
|-------------|------------|------------------|----|------------------|-----------------------|------|-------------|---------|
| ANID520150W | Develosil  | ANIDIUS          | 5  | Semi micoro      | 2.0                   | 150  | 52,000      |         |
| ANID520250W | Develosil  | ANIDIUS          | 5  | Semi micoro      | 2.0                   | 250  | 62,000      |         |
| ANID546150W | Develosil  | ANIDIUS          | 5  | Analysis column  | (Conventional Column) | 4.6  | 150         | 52,000  |
| ANID546250W | Develosil  | ANIDIUS          | 5  | Analysis column  | (Conventional Column) | 4.6  | 250         | 62,000  |
| ANID5P1150W | Develosil  | ANIDIUS          | 5  | Semi-preparative |                       | 10.0 | 150         | 120,000 |
| ANID5P1250W | Develosil  | ANIDIUS          | 5  | Semi-preparative |                       | 10.0 | 250         | 160,000 |
| ANID5P2150W | Develosil  | ANIDIUS          | 5  | preparative      |                       | 20.0 | 150         | 240,000 |
| ANID5P2250W | Develosil  | ANIDIUS          | 5  | preparative      |                       | 20.0 | 250         | 320,000 |

### Develosil ANIDIUS Guard column

| Part number           | Brand name | Stationary phase  | um | Column category                | I.D.                           | mm   | price (yen) |           |           |
|-----------------------|------------|---|----|--------------------------------|--------------------------------|------|-------------|-----------|-----------|
|                       |            |   |    |                                |                                |      | old price   | New price |           |
| <b>cartridge type</b> |            |   |    |                                |                                |      |             |           |           |
| HO00015010C           | Develosil  | Guard cartridge holder  |    | Holder for the guard cartridge | for i.d. 1.0mm,1.5mm and 2.0mm | 1.5  | 10          | 15,000    | 18,000    |
| HO00040010C           | Develosil  | Guard cartridge holder  |    | Holder for the guard cartridge | for i.d. 4.0mm,4.6mm and 6.0mm | 4.0  | 10          | 9,500     | 13,000    |
| ANID515010W           | Develosil  | ANIDIUS-S Guard cartridge set<br>Holder(1piece) + cartridge 10 x 1.5mm (1piece) | 5  | The gured column               | for i.d. 1.0mm,1.5mm and 2.0mm | 1.5  | 10          | 20,000    | 25,500    |
| ANID515010C           | Develosil  | ANIDIUS-S Guard cartridge <b>[4/pk]</b>   | 5  | The cartridge for exchange     | for i.d. 1.0mm,1.5mm and 2.0mm | 1.5  | 10          | 20,000    | 30,000    |
| ANID540010W           | Develosil  | ANIDIUS Guard cartridge set<br>Holder(1piece) + cartridge 10 x 4.0mm (1piece)   | 5  | The gurad column               | for i.d. 4.0mm,4.6mm and 6.0mm | 4.0  | 10          | 14,000    | 24,000    |
| ANID540010C           | Develosil  | ANIDIUS Guard cartridge <b>[4/pk]</b>   | 5  | The cartridge for exchange     | for i.d. 4.0mm,4.6mm and 6.0mm | 4.0  | 10          | 18,000    | 30,000    |
| <b>filling type</b>   |            |   |    |                                |                                |      |             |           |           |
| ANID580010W           | Develosil  | ANIDIUS   | 5  | The gurad column               | for i.d. 8.0mm and 10.0mm      | 8.0  | 10          | 20,000    | no change |
| ANID5P2050W           | Develosil  | ANIDIUS   | 5  | The gurad column               | for i.d. 20.0mm                | 20.0 | 50          | 110,000   | no change |