

Develosil XG-C18

Part number	Brand name	Stationary phase	um	Column category	i.d.	mm	price (yen)	
XG18M320035W	Develosil	XG-C18M-3	3	Semi micoro		2.0	35	32,000
XG18M320050W	Develosil	XG-C18M-3	3	Semi micoro		2.0	50	34,000
XG18M320075W	Develosil	XG-C18M-3	3	Semi micoro		2.0	75	37,000
XG18M320100W	Develosil	XG-C18M-3	3	Semi micoro		2.0	100	41,000
XG18M320150W	Develosil	XG-C18M-3	3	Semi micoro		2.0	150	47,000
XG18M320250W	Develosil	XG-C18M-3	3	Semi micoro		2.0	250	61,000
XG18M520035W	Develosil	XG-C18M-5	5	Semi micoro		2.0	35	30,000
XG18M520050W	Develosil	XG-C18M-5	5	Semi micoro		2.0	50	32,000
XG18M520075W	Develosil	XG-C18M-5	5	Semi micoro		2.0	75	35,000
XG18M520100W	Develosil	XG-C18M-5	5	Semi micoro		2.0	100	39,000
XG18M520150W	Develosil	XG-C18M-5	5	Semi micoro		2.0	150	45,000
XG18M520250W	Develosil	XG-C18M-5	5	Semi micoro		2.0	250	59,000
XG18M346035W	Develosil	XG-C18M-3	3	Analysis column	(Conventional Column)	4.6	35	32,000
XG18M346050W	Develosil	XG-C18M-3	3	Analysis column	(Conventional Column)	4.6	50	34,000
XG18M346075W	Develosil	XG-C18M-3	3	Analysis column	(Conventional Column)	4.6	75	37,000
XG18M346100W	Develosil	XG-C18M-3	3	Analysis column	(Conventional Column)	4.6	100	41,000
XG18M346150W	Develosil	XG-C18M-3	3	Analysis column	(Conventional Column)	4.6	150	47,000
XG18M346250W	Develosil	XG-C18M-3	3	Analysis column	(Conventional Column)	4.6	250	61,000
XG18M546035W	Develosil	XG-C18M-5	5	Analysis column	(Conventional Column)	4.6	35	30,000
XG18M546050W	Develosil	XG-C18M-5	5	Analysis column	(Conventional Column)	4.6	50	32,000
XG18M546075W	Develosil	XG-C18M-5	5	Analysis column	(Conventional Column)	4.6	75	35,000
XG18M546100W	Develosil	XG-C18M-5	5	Analysis column	(Conventional Column)	4.6	100	39,000
XG18M546150W	Develosil	XG-C18M-5	5	Analysis column	(Conventional Column)	4.6	150	45,000
XG18M546250W	Develosil	XG-C18M-5	5	Analysis column	(Conventional Column)	4.6	250	59,000
XG18M5P1150W	Develosil	XG-C18M-5	5	Semi-preparative		10.0	150	140,000
XG18M5P1250W	Develosil	XG-C18M-5	5	Semi-preparative		10.0	250	156,000
XG18M5P2150W	Develosil	XG-C18M-5	5	preparative		20.0	150	245,000
XG18M5P2250W	Develosil	XG-C18M-5	5	preparative		20.0	250	320,000

Develosil XG-C18 Guard column

Part number	Brand name	Stationary phase	um	Column category	I.D.	mm	price (yen)		
							old price	New price	
cartridge type									
HO00015010C	Develosil	Guard cartridge holder		Holder for the guard cartridge	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	15,000	18,000
HO00040010C	Develosil	Guard cartridge holder		Holder for the guard cartridge	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	9,500	13,000
XG18515010W	Develosil	XG-C18-S Guard cartridge set Holder(1piece) + cartridge 10 x 1.5mm (1piece)	5	The gured column	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	20,000	25,500
XG18515010C	Develosil	XG-C18-S Guard cartridge 【4/pk】	5	The cartridge for exchange	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	20,000	30,000
XG18540010W	Develosil	XG-C18 Guard cartridge set Holder(1piece) + cartridge 10 x 4.0mm (1piece)	5	The gurad column	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	14,000	24,000
XG18540010C	Develosil	XG-C18 Guard cartridge 【4/pk】	5	The cartridge for exchange	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	1,800	30,000
filling type									
XG18M580010W	Develosil	XG-C18M-5	5	The gurad column	for i.d. 8.0mm and 10.0mm	8.0	10	20,000	no change
XG18M5P2050W	Develosil	XG-C18M-5	5	The gurad column	for i.d. 20.0mm	20.0	50	100,000	no change

Develosil XG-C30

Part number	Brand name	Stationary phase	um	Column category	i.d.	mm	price (yen)	
XG30M320035W	Develosil	XG-C30M-3	3	Semi micoro		2.0	35	42,000
XG30M320050W	Develosil	XG-C30M-3	3	Semi micoro		2.0	50	44,000
XG30M320075W	Develosil	XG-C30M-3	3	Semi micoro		2.0	75	47,000
XG30M320100W	Develosil	XG-C30M-3	3	Semi micoro		2.0	100	52,000
XG30M320150W	Develosil	XG-C30M-3	3	Semi micoro		2.0	150	62,000
XG30M320250W	Develosil	XG-C30M-3	3	Semi micoro		2.0	250	72,000
XG30M520035W	Develosil	XG-C30M-5	5	Semi micoro		2.0	35	37,000
XG30M520050W	Develosil	XG-C30M-5	5	Semi micoro		2.0	50	40,000
XG30M520075W	Develosil	XG-C30M-5	5	Semi micoro		2.0	75	42,000
XG30M520100W	Develosil	XG-C30M-5	5	Semi micoro		2.0	100	47,000
XG30M520150W	Develosil	XG-C30M-5	5	Semi micoro		2.0	150	57,000
XG30M520250W	Develosil	XG-C30M-5	5	Semi micoro		2.0	250	67,000
XG30M346035W	Develosil	XG-C30M-3	3	Analysis column	(Conventional Column)	4.6	35	42,000
XG30M346050W	Develosil	XG-C30M-3	3	Analysis column	(Conventional Column)	4.6	50	44,000
XG30M346075W	Develosil	XG-C30M-3	3	Analysis column	(Conventional Column)	4.6	75	47,000
XG30M346100W	Develosil	XG-C30M-3	3	Analysis column	(Conventional Column)	4.6	100	52,000
XG30M346150W	Develosil	XG-C30M-3	3	Analysis column	(Conventional Column)	4.6	150	62,000
XG30M346250W	Develosil	XG-C30M-3	3	Analysis column	(Conventional Column)	4.6	250	72,000
XG30M546035W	Develosil	XG-C30M-5	5	Analysis column	(Conventional Column)	4.6	35	37,000
XG30M546050W	Develosil	XG-C30M-5	5	Analysis column	(Conventional Column)	4.6	50	40,000
XG30M546075W	Develosil	XG-C30M-5	5	Analysis column	(Conventional Column)	4.6	75	42,000
XG30M546100W	Develosil	XG-C30M-5	5	Analysis column	(Conventional Column)	4.6	100	47,000
XG30M546150W	Develosil	XG-C30M-5	5	Analysis column	(Conventional Column)	4.6	150	57,000
XG30M546250W	Develosil	XG-C30M-5	5	Analysis column	(Conventional Column)	4.6	250	67,000
XG30M5P1150W	Develosil	XG-C30M-5	5	Semi-preparative		10.0	150	150,000
XG30M5P1250W	Develosil	XG-C30M-5	5	Semi-preparative		10.0	250	165,000
XG30M5P2150W	Develosil	XG-C30M-5	5	preparative		20.0	150	250,000
XG30M5P2250W	Develosil	XG-C30M-5	5	preparative		20.0	250	325,000

Develosil XG-C30 Guard column

Part number	Brand name	Stationary phase	um	Column category	I.D.	mm	price (yen)		
							old price	New price	
cartridge type									
HO00015010C	Develosil	Guard cartridge holder		Holder for the guard cartridge	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	15,000	18,000
HO00040010C	Develosil	Guard cartridge holder		Holder for the guard cartridge	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	9,500	13,000
XG30515010W	Develosil	XG-C30-S Guard cartridge set Holder(1piece) + cartridge 10 x 1.5mm (1piece)	5	The gured column	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	20,000	25,500
XG30515010C	Develosil	XG-C30-S Guard cartridge 【4/pk】	5	The cartridge for exchange	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	20,000	30,000
XG30540010W	Develosil	XG-C30 Guard cartridge set Holder(1piece) + cartridge 10 x 4.0mm (1piece)	5	The gurad column	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	14,000	24,000
XG30540010C	Develosil	XG-C30 Guard cartridge 【4/pk】	5	The cartridge for exchange	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	18,000	30,000
filling type									
XG30M580010W	Develosil	XG-C30M-5	5	The gurad column	for i.d. 8.0mm and 10.0mm	8.0	10	20,000	no change
XG30M5P2050W	Develosil	XG-C18M-5	5	The gurad column	for i.d. 20.0mm	20.0	50	115,000	no change

Develosil XG-CN

Part number	Brand name	Stationary phase	um	Column category	i.d.	mm	price (yen)	
XGCN320035W	Develosil	XG-CN-3	3	Semi micoro		2.0	35	38,000
XGCN320050W	Develosil	XG-CN-3	3	Semi micoro		2.0	50	38,000
XGCN320075W	Develosil	XG-CN-3	3	Semi micoro		2.0	75	43,000
XGCN320100W	Develosil	XG-CN-3	3	Semi micoro		2.0	100	48,000
XGCN320150W	Develosil	XG-CN-3	3	Semi micoro		2.0	150	58,000
XGCN320250W	Develosil	XG-CN-3	3	Semi micoro		2.0	250	68,000
XGCN520035W	Develosil	XG-CN-5	5	Semi micoro		2.0	35	35,000
XGCN520050W	Develosil	XG-CN-5	5	Semi micoro		2.0	50	35,000
XGCN520075W	Develosil	XG-CN-5	5	Semi micoro		2.0	75	40,000
XGCN520100W	Develosil	XG-CN-5	5	Semi micoro		2.0	100	45,000
XGCN520150W	Develosil	XG-CN-5	5	Semi micoro		2.0	150	55,000
XGCN520250W	Develosil	XG-CN-5	5	Semi micoro		2.0	250	65,000
XGCN346035W	Develosil	XG-CN-3	3	Analysis column	(Conventional Column)	4.6	35	38,000
XGCN346050W	Develosil	XG-CN-3	3	Analysis column	(Conventional Column)	4.6	50	38,000
XGCN346075W	Develosil	XG-CN-3	3	Analysis column	(Conventional Column)	4.6	75	43,000
XGCN346100W	Develosil	XG-CN-3	3	Analysis column	(Conventional Column)	4.6	100	48,000
XGCN346150W	Develosil	XG-CN-3	3	Analysis column	(Conventional Column)	4.6	150	58,000
XGCN346250W	Develosil	XG-CN-3	3	Analysis column	(Conventional Column)	4.6	250	68,000
XGCN546035W	Develosil	XG-CN-5	5	Analysis column	(Conventional Column)	4.6	35	35,000
XGCN546050W	Develosil	XG-CN-5	5	Analysis column	(Conventional Column)	4.6	50	35,000
XGCN546075W	Develosil	XG-CN-5	5	Analysis column	(Conventional Column)	4.6	75	40,000
XGCN546100W	Develosil	XG-CN-5	5	Analysis column	(Conventional Column)	4.6	100	45,000
XGCN546150W	Develosil	XG-CN-5	5	Analysis column	(Conventional Column)	4.6	150	55,000
XGCN546250W	Develosil	XG-CN-5	5	Analysis column	(Conventional Column)	4.6	250	65,000
XGCN5P1150W	Develosil	XG-CN-5	5	Semi-preparative		10.0	150	130,000
XGCN5P1250W	Develosil	XG-CN-5	5	Semi-preparative		10.0	250	150,000
XGCN5P2150W	Develosil	XG-CN-5	5	preparative		20.0	150	240,000
XGCN5P2250W	Develosil	XG-CN-5	5	preparative		20.0	250	275,000

Develosil XG-CN Guard column

Part number	Brand name	Stationary phase	um	Column category	I.D.	mm	price (yen)		
							old price	New price	
cartridge type									
HO00015010C	Develosil	Guard cartridge holder		Holder for the guard cartridge	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	15,000	18,000
HO00040010C	Develosil	Guard cartridge holder		Holder for the guard cartridge	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	9,500	13,000
XGCN515010W	Develosil	XG-CN-S Guard cartridge set Holder(1piece) + cartridge 10 x 1.5mm (1piece)	5	The gured column	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	20,000	25,500
XGCN515010C	Develosil	XG-CN-S Guard cartridge 【4/pk】	5	The cartridge for exchange	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	20,000	30,000
XGCN540010W	Develosil	XG-CN Guard cartridge set Holder(1piece) + cartridge 10 x 4.0mm (1piece)	5	The gurad column	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	14,000	24,000
XGCN540010C	Develosil	XG-CN Guard cartridge 【4/pk】	5	The cartridge for exchange	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	18,000	30,000
filling type									
XGCN580010W	Develosil	XG-CN-5	5	The gurad column	for i.d. 8.0mm and 10.0mm	8.0	10	20,000	no change
XGCN5P2050W	Develosil	XG-CN-5	5	The gurad column	for i.d. 20.0mm	20.0	50	105,000	no change

Develosil XG-C1

Part number	Brand name	Stationary phase	um	Column category	i.d.	mm	price (yen)	
XGC1320035W	Develosil	XG-C1-3	3	Semi micoro		2.0	35	31,000
XGC1320050W	Develosil	XG-C1-3	3	Semi micoro		2.0	50	33,000
XGC1320075W	Develosil	XG-C1-3	3	Semi micoro		2.0	75	39,500
XGC1320100W	Develosil	XG-C1-3	3	Semi micoro		2.0	100	46,000
XGC1320150W	Develosil	XG-C1-3	3	Semi micoro		2.0	150	51,000
XGC1320250W	Develosil	XG-C1-3	3	Semi micoro		2.0	250	65,000
XGC1520035W	Develosil	XG-C1-5	5	Semi micoro		2.0	35	28,000
XGC1520050W	Develosil	XG-C1-5	5	Semi micoro		2.0	50	30,000
XGC1520075W	Develosil	XG-C1-5	5	Semi micoro		2.0	75	36,500
XGC1520100W	Develosil	XG-C1-5	5	Semi micoro		2.0	100	43,000
XGC1520150W	Develosil	XG-C1-5	5	Semi micoro		2.0	150	48,000
XGC1520250W	Develosil	XG-C1-5	5	Semi micoro		2.0	250	60,000
XGC1346035W	Develosil	XG-C1-3	3	Analysis column	(Conventional Column)	4.6	35	31,000
XGC1346050W	Develosil	XG-C1-3	3	Analysis column	(Conventional Column)	4.6	50	33,000
XGC1346075W	Develosil	XG-C1-3	3	Analysis column	(Conventional Column)	4.6	75	39,500
XGC1346100W	Develosil	XG-C1-3	3	Analysis column	(Conventional Column)	4.6	100	46,000
XGC1346150W	Develosil	XG-C1-3	3	Analysis column	(Conventional Column)	4.6	150	51,000
XGC1346250W	Develosil	XG-C1-3	3	Analysis column	(Conventional Column)	4.6	250	65,000
XGC1546035W	Develosil	XG-C1-5	5	Analysis column	(Conventional Column)	4.6	35	28,000
XGC1546050W	Develosil	XG-C1-5	5	Analysis column	(Conventional Column)	4.6	50	30,000
XGC1546075W	Develosil	XG-C1-5	5	Analysis column	(Conventional Column)	4.6	75	36,500
XGC1546100W	Develosil	XG-C1-5	5	Analysis column	(Conventional Column)	4.6	100	43,000
XGC1546150W	Develosil	XG-C1-5	5	Analysis column	(Conventional Column)	4.6	150	48,000
XGC1546250W	Develosil	XG-C1-5	5	Analysis column	(Conventional Column)	4.6	250	60,000
XGC15P1150W	Develosil	XG-C1-5	5	Semi-preparative		10.0	150	120,000
XGC15P1250W	Develosil	XG-C1-5	5	Semi-preparative		10.0	250	140,000
XGC15P2150W	Develosil	XG-C1-5	5	preparative		20.0	150	245,000
XGC15P2250W	Develosil	XG-C1-5	5	preparative		20.0	250	300,000

Develosil XG-C1 Guard column

Part number	Brand name	Stationary phase	um	Column category	I.D.	mm	price (yen)		
							old price	New price	
cartridge type									
HO00015010C	Develosil	Guard cartridge holder		Holder for the guard cartridge	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	15,000	18,000
HO00040010C	Develosil	Guard cartridge holder		Holder for the guard cartridge	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	9,500	13,000
XGC1515010W	Develosil	XG-C1-S Guard cartridge set Holder(1piece) + cartridge 10 x 1.5mm (1piece)	5	The gured column	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	20,000	25,500
XGC1515010C	Develosil	XG-C1-S Guard cartridge 【4/pk】	5	The cartridge for exchange	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	20,000	30,000
XGC1540010W	Develosil	XG-C1 Guard cartridge set Holder(1piece) + cartridge 10 x 4.0mm (1piece)	5	The gurad column	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	14,000	24,000
XGC1540010C	Develosil	XG-C1 Guard cartridge 【4/pk】	5	The cartridge for exchange	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	18,000	30,000
filling type									
XGC1580010W	Develosil	XG-C1-5	5	The gurad column	for i.d. 8.0mm and 10.0mm	8.0	10	20,000	no change
XGC15P2050W	Develosil	XG-C1-5	5	The gurad column	for i.d. 20.0mm	20.0	50	115,000	no change

Develosil XG-C18LC

Part number	Brand name	Stationary phase	um	Column category	i.d.	mm	price (yen)	
55-320035W	Develosil	XG-C18LC-3	3	Semi micoro		2.0	35	32,000
55-320050W	Develosil	XG-C18LC-3	3	Semi micoro		2.0	50	34,000
55-320075W	Develosil	XG-C18LC-3	3	Semi micoro		2.0	75	37,000
55-320100W	Develosil	XG-C18LC-3	3	Semi micoro		2.0	100	41,000
55-320150W	Develosil	XG-C18LC-3	3	Semi micoro		2.0	150	47,000
55-320250W	Develosil	XG-C18LC-3	3	Semi micoro		2.0	250	61,000
55-520035W	Develosil	XG-C18LC-5	5	Semi micoro		2.0	35	30,000
55-520050W	Develosil	XG-C18LC-5	5	Semi micoro		2.0	50	32,000
55-520075W	Develosil	XG-C18LC-5	5	Semi micoro		2.0	75	35,000
55-520100W	Develosil	XG-C18LC-5	5	Semi micoro		2.0	100	39,000
55-520150W	Develosil	XG-C18LC-5	5	Semi micoro		2.0	150	45,000
55-520250W	Develosil	XG-C18LC-5	5	Semi micoro		2.0	250	59,000
55-346035W	Develosil	XG-C18LC-3	3	Analysis column	(Conventional Column)	4.6	35	32,000
55-346050W	Develosil	XG-C18LC-3	3	Analysis column	(Conventional Column)	4.6	50	34,000
55-346075W	Develosil	XG-C18LC-3	3	Analysis column	(Conventional Column)	4.6	75	37,000
55-346100W	Develosil	XG-C18LC-3	3	Analysis column	(Conventional Column)	4.6	100	41,000
55-346150W	Develosil	XG-C18LC-3	3	Analysis column	(Conventional Column)	4.6	150	47,000
55-346250W	Develosil	XG-C18LC-3	3	Analysis column	(Conventional Column)	4.6	250	61,000
55-546035W	Develosil	XG-C18LC-5	5	Analysis column	(Conventional Column)	4.6	35	30,000
55-546050W	Develosil	XG-C18LC-5	5	Analysis column	(Conventional Column)	4.6	50	32,000
55-546075W	Develosil	XG-C18LC-5	5	Analysis column	(Conventional Column)	4.6	75	35,000
55-546100W	Develosil	XG-C18LC-5	5	Analysis column	(Conventional Column)	4.6	100	39,000
55-546150W	Develosil	XG-C18LC-5	5	Analysis column	(Conventional Column)	4.6	150	45,000
55-546250W	Develosil	XG-C18LC-5	5	Analysis column	(Conventional Column)	4.6	250	59,000
55-5P1150W	Develosil	XG-C18LC-5	5	Semi-preparative		10.0	150	140,000
55-5P1250W	Develosil	XG-C18LC-5	5	Semi-preparative		10.0	250	156,000
55-5P2150W	Develosil	XG-C18LC-5	5	preparative		20.0	150	245,000
55-5P2250W	Develosil	XG-C18LC-5	5	preparative		20.0	250	320,000

Develosil XG-C18LC Guard column

Part number	Brand name	Stationary phase	um	Column category	I.D.	mm	price (yen)		
							old price	New price	
cartridge type									
HO00015010C	Develosil	Guard cartridge holder		Holder for the guard cartridge	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	15,000	18,000
HO00040010C	Develosil	Guard cartridge holder		Holder for the guard cartridge	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	9,500	13,000
55-515010W	Develosil	XG-C18LC-S Guard cartridge set Holder(1piece) + cartridge 10 x 1.5mm (1piece)	5	The gured column	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	20,000	25,500
55-515010C	Develosil	XG-C18LC-S Guard cartridge 【4/pk】	5	The cartridge for exchange	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	20,000	30,000
55-540010W	Develosil	XG-C18LC Guard cartridge set Holder(1piece) + cartridge 10 x 4.0mm (1piece)	5	The gurad column	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	14,000	24,000
55-540010C	Develosil	XG-C18LC Guard cartridge 【4/pk】	5	The cartridge for exchange	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	18,000	30,000
filling type									
55-580010W	Develosil	XG-C18LC-5	5	The gurad column	for i.d. 8.0mm and 10.0mm	8.0	10	20,000	no change
55-5P2050W	Develosil	XG-C18LC-5	5	The gurad column	for i.d. 20.0mm	20.0	50	100,000	no change