

## Develosil HSR AQ C18

Part number	Brand name	Stationary phase	um		Column category	I.D.	mm	price (yen)
73-320050W	Develosil	HSR AQ C18-3	3	Semi micoro		2.0	50	40,000
73-320075W	Develosil	HSR AQ C18-3	3	Semi micoro		2.0	75	42,000
73-320100W	Develosil	HSR AQ C18-3	3	Semi micoro		2.0	100	45,000
73-320150W	Develosil	HSR AQ C18-3	3	Semi micoro		2.0	150	55,000
73-320250W	Develosil	HSR AQ C18-3	3	Semi micoro		2.0	250	67,000
73-520050W	Develosil	HSR AQ C18-5	5	Semi micoro		2.0	50	37,000
73-520075W	Develosil	HSR AQ C18-5	5	Semi micoro		2.0	75	39,000
73-520100W	Develosil	HSR AQ C18-5	5	Semi micoro		2.0	100	42,000
73-520150W	Develosil	HSR AQ C18-5	5	Semi micoro		2.0	150	52,000
73-520250W	Develosil	HSR AQ C18-5	5	Semi micoro		2.0	250	62,000
73-330050W	Develosil	HSR AQ C18-3	3	Analysis column	(Conventional Column)	3.0	50	40,000
73-330075W	Develosil	HSR AQ C18-3	3	Analysis column	(Conventional Column)	3.0	75	42,000
73-330100W	Develosil	HSR AQ C18-3	3	Analysis column	(Conventional Column)	3.0	100	45,000
73-330150W	Develosil	HSR AQ C18-3	3	Analysis column	(Conventional Column)	3.0	150	55,000
73-330250W	Develosil	HSR AQ C18-3	3	Analysis column	(Conventional Column)	3.0	250	67,000
73-346050W	Develosil	HSR AQ C18-3	3	Analysis column	(Conventional Column)	4.6	50	40,000
73-346075W	Develosil	HSR AQ C18-3	3	Analysis column	(Conventional Column)	4.6	75	42,000
73-346100W	Develosil	HSR AQ C18-3	3	Analysis column	(Conventional Column)	4.6	100	45,000
73-346150W	Develosil	HSR AQ C18-3	3	Analysis column	(Conventional Column)	4.6	150	55,000
73-346250W	Develosil	HSR AQ C18-3	3	Analysis column	(Conventional Column)	4.6	250	67,000
73-530050W	Develosil	HSR AQ C18-5	5	Analysis column	(Conventional Column)	3.0	50	37,000
73-530075W	Develosil	HSR AQ C18-5	5	Analysis column	(Conventional Column)	3.0	75	39,000
73-530100W	Develosil	HSR AQ C18-5	5	Analysis column	(Conventional Column)	3.0	100	42,000
73-530150W	Develosil	HSR AQ C18-5	5	Analysis column	(Conventional Column)	3.0	150	52,000
73-530250W	Develosil	HSR AQ C18-5	5	Analysis column	(Conventional Column)	3.0	250	62,000
73-546050W	Develosil	HSR AQ C18-5	5	Analysis column	(Conventional Column)	4.6	50	37,000
73-546075W	Develosil	HSR AQ C18-5	5	Analysis column	(Conventional Column)	4.6	75	39,000
73-546100W	Develosil	HSR AQ C18-5	5	Analysis column	(Conventional Column)	4.6	100	42,000
73-546150W	Develosil	HSR AQ C18-5	5	Analysis column	(Conventional Column)	4.6	150	52,000
73-546250W	Develosil	HSR AQ C18-5	5	Analysis column	(Conventional Column)	4.6	250	62,000
73-580250W	Develosil	HSR AQ C18-5	5	Semi-preparative		8.0	250	110,000
73-5P1250W	Develosil	HSR AQ C18-5	5	Semi-preparative		10.0	250	160,000
73-5P2250W	Develosil	HSR AQ C18-5	5	preparative		20.0	250	320,000

## Develosil HSR AQ C18 Guard column

Part number	Brand name	Stationary phase	um		Column category	I.D.	mm	price (yen)
<b>cartridge type</b>								
HO00015010C	Develosil	Guard cartridge holder		Holder for the guard cartridge	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	18,000
HO00040010C	Develosil	Guard cartridge holder		Holder for the guard cartridge	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	13,000
73-515010W	Develosil	HSR AQ C18-S Guard cartridge set Holder(1piece) + cartridge 10 x 1.5mm (1piece)	5	The gured column	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	25,500
73-515010C	Develosil	HSR AQ C18-S Guard cartridge 【4/pk】	5	The cartridge for exchange	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	30,000
73-540010W	Develosil	HSR AQ C18 Guard cartridge set Holder(1piece) + cartridge 10 x 4.0mm (1piece)	5	The gurad column	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	24,000
73-540010C	Develosil	HSR AQ C18 Guard cartridge 【4/pk】	5	The cartridge for exchange	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	30,000
<b>filling type</b>								
73-580010W	Develosil	HSR AQ C18-5	5	The gurad column	for i.d. 8.0mm and 10.0mm	8.0	10	20,000
73-5P2050W	Develosil	HSR AQ C18-5	5	The gurad column	for i.d. 20.0mm	20.0	50	110,000

## Develosil HSR C1

Part number	Brand name	Stationary phase	um		Column category	I.D.	mm	price (yen)
74-320050W	Develosil	HSR C1-3	3	Semi micoro		2.0	50	40,000
74-320075W	Develosil	HSR C1-3	3	Semi micoro		2.0	75	42,000
74-320100W	Develosil	HSR C1-3	3	Semi micoro		2.0	100	45,000
74-320150W	Develosil	HSR C1-3	3	Semi micoro		2.0	150	55,000
74-320250W	Develosil	HSR C1-3	3	Semi micoro		2.0	250	67,000
74-520050W	Develosil	HSR C1-5	5	Semi micoro		2.0	50	37,000
74-520075W	Develosil	HSR C1-5	5	Semi micoro		2.0	75	39,000
74-520100W	Develosil	HSR C1-5	5	Semi micoro		2.0	100	42,000
74-520150W	Develosil	HSR C1-5	5	Semi micoro		2.0	150	52,000
74-520250W	Develosil	HSR C1-5	5	Semi micoro		2.0	250	62,000
74-330050W	Develosil	HSR C1-3	3	Analysis column	(Conventional Column)	3.0	50	40,000
74-330075W	Develosil	HSR C1-3	3	Analysis column	(Conventional Column)	3.0	75	42,000
74-330100W	Develosil	HSR C1-3	3	Analysis column	(Conventional Column)	3.0	100	45,000
74-330150W	Develosil	HSR C1-3	3	Analysis column	(Conventional Column)	3.0	150	55,000
74-330250W	Develosil	HSR C1-3	3	Analysis column	(Conventional Column)	3.0	250	67,000
74-346050W	Develosil	HSR C1-3	3	Analysis column	(Conventional Column)	4.6	50	40,000
74-346075W	Develosil	HSR C1-3	3	Analysis column	(Conventional Column)	4.6	75	42,000
74-346100W	Develosil	HSR C1-3	3	Analysis column	(Conventional Column)	4.6	100	45,000
74-346150W	Develosil	HSR C1-3	3	Analysis column	(Conventional Column)	4.6	150	55,000
74-346250W	Develosil	HSR C1-3	3	Analysis column	(Conventional Column)	4.6	250	67,000
74-530050W	Develosil	HSR C1-5	5	Analysis column	(Conventional Column)	3.0	50	37,000
74-530075W	Develosil	HSR C1-5	5	Analysis column	(Conventional Column)	3.0	75	39,000
74-530100W	Develosil	HSR C1-5	5	Analysis column	(Conventional Column)	3.0	100	42,000
74-530150W	Develosil	HSR C1-5	5	Analysis column	(Conventional Column)	3.0	150	52,000
74-530250W	Develosil	HSR C1-5	5	Analysis column	(Conventional Column)	3.0	250	62,000
74-546050W	Develosil	HSR C1-5	5	Analysis column	(Conventional Column)	4.6	50	37,000
74-546075W	Develosil	HSR C1-5	5	Analysis column	(Conventional Column)	4.6	75	39,000
74-546100W	Develosil	HSR C1-5	5	Analysis column	(Conventional Column)	4.6	100	42,000
74-546150W	Develosil	HSR C1-5	5	Analysis column	(Conventional Column)	4.6	150	52,000
74-546250W	Develosil	HSR C1-5	5	Analysis column	(Conventional Column)	4.6	250	62,000
74-580250W	Develosil	HSR C1-5	5	Semi-preparative		8.0	250	110,000
74-5P1250W	Develosil	HSR C1-5	5	Semi-preparative		10.0	250	160,000
74-5P2250W	Develosil	HSR C1-5	5	preparative		20.0	250	320,000

## Develosil HSR C1 Guard column

Part number	Brand name	Stationary phase	um		Column category	I.D.	mm	price (yen)
<b>cartridge type</b>								
HO00015010C	Develosil	Guard cartridge holder		Holder for the guard cartridge	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	18,000
HO00040010C	Develosil	Guard cartridge holder		Holder for the guard cartridge	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	13,000
74-515010W	Develosil	HSR C1-S Guard cartridge set Holder(1piece) + cartridge 10 x 1.5mm (1piece)	5	The gured column	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	25,500
74-515010C	Develosil	HSR C1-S Guard cartridge 【4/pk】	5	The cartridge for exchange	for i.d. 1.0mm,1.5mm and 2.0mm	1.5	10	30,000
74-540010W	Develosil	HSR C1 Guard cartridge set Holder(1piece) + cartridge 10 x 4.0mm (1piece)	5	The gurad column	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	24,000
74-540010C	Develosil	HSR C1 Guard cartridge 【4/pk】	5	The cartridge for exchange	for i.d. 4.0mm,4.6mm and 6.0mm	4.0	10	30,000
<b>filling type</b>								
74-580010W	Develosil	HSR C1-5	5	The gurad column	for i.d. 8.0mm and 10.0mm	8.0	10	20,000
74-5P2050W	Develosil	HSR C1-5	5	The gurad column	for i.d. 20.0mm	20.0	50	110,000